

Tygon S3™ A24, A24-C

Vacuum Tubing for Milking Equipment

Reduced Maintenance and Inspection Concerns

Tygon S3 A24 tubing is ideally suited for supply air transport. The smooth inner surface is less susceptible to particle entrapment, which can restrict air flow, while crystal clarity permits detection of equipment deficiencies such as backflow of milk into the air lines. Tygon S3 A24 tubing is designed to work in tandem with Tygon S3 M-34-R tubing to provide vacuum and easy flow within the milking process.

The Mark of Quality

Every foot of Tygon S3 A24 tubing has been embedded with a trademark stripe within the tubing walls. The embedded stripe is your assurance of receiving genuine Tygon S3 tubing, the world's finest raw milk tubing produced specifically for the dairy industry.



Features and Benefits

- Holds full vacuum at room temperature
- Will not crack and age like rubber tubing
- Lightweight and flexible for quick installation
- Non-wetting properties allow easy cleaning and complete drainage
- Durability for long and reliable service
- Contains no BPA or phthalates
- To be used in conjunction with Tygon S3 M-34-R

Typical Applications*

- Raw milk transport lines
- Dairy processing

Relative Chemical Resistance Properties*

Acids			Bases			Salts	Alcohols	Ketones
Conc.	Med.	Weak	Conc.	Med.	Weak			
F	E	E	U	E	E	E	F	U

E = Excellent F = Fair U = Unsatisfactory

*All tests conducted at room temperature

Tubing Properties

Min. Bend Radius, inch (mm)	1-1/8 (28.57)
Max. Working Pressure at 73°F, psi (bar)	25 (1.7)
Vacuum Rating at 73°F, inHg (mmHg)	29.9 (760)

Product Characteristics

Opacity	A24 A24-C	Transparent Opaque
---------	--------------	-----------------------

Typical Physical Properties

Property	ASTM Method	Value or Rating
Durometer Hardness, (Shore A), 15 sec	D2240	56
Color	A24 A24-C	— Clear Black
Tensile Strength, psi (MPa)	D412	1755 (12.1)
Ultimate Elongation, %	D412	425
Tear Resistance, lb-f/in (kN/m)	D1004	177 (31.0)
Specific Gravity	D792	1.21
Water Absorption, % at 73°F (23°C) for 24 hrs.	D570	0.21
Compression Set Constant Deflection, % at 158°F (70°C) for 22 hrs.	D395 Method B	64
Maximum Recommended Operating Temp., °F (°C)	—	165 (74)
Brittleness by Impact Temp., °F (°C)	D746	-32 (-36)
Tensile Stress, psi (MPa) @ 100% Elongation	D412	580 (4.0)
Tensile Set, %	D412	95

Unless otherwise noted, all tests were conducted at room temperature (73°F). Values shown were determined on 0.075" thick extruded strip or 0.075" thick molded ASTM plaques or molded ASTM durometer buttons.

Tygon S3™ A24, A24-C Tubing Cleaning Instructions

To extend the usable life of Tygon S3 A 24, A24-C tubing and reduce the risk of bacterial growth resulting from a buildup of milksoil film, the following cleaning and sanitary procedures must be followed:

1. Following milking and dumping, rinse tubing with clean water at (43°C) without recirculating until discharge is clear.
2. Wash tubing with alkaline cleaner (containing no caustic soda) for 10-15 minutes at (65°C); final dump temperature should not be below (43°C).
3. Use an acid rise to prevent milkstone deposits.
 - a. Perform daily after each cleaning for 5 minutes with cold- to room-temperature water.
 - b. Perform a once-weekly acid rinse for 15 minutes with (43°C) to (60°C) water in place of the alkaline cleaner used in Step 2.
4. Purge moisture by draining and passing warm filtered air through the tubing until complete dryness is achieved.
5. Sanitize tubing immediately prior to use following the manufacturer's recommended procedures.

The values listed for working and burst pressures are derived from tests conducted under controlled laboratory conditions. Many factors will reduce the tubing's ability to withstand pressures, including temperature, chemical attack, stress, pulsation and the attachment to fittings. It is imperative that the user conduct tests simulating the conditions of the application prior to specifying the tubing for use.

TYGON S3™ A24, A24-C TUBING ARE NOT INTENDED FOR USE AS AN IMPLANT MATERIAL.

www.ics.saint-gobain.com



Saint-Gobain Performance Plastics
2664 Gilchrist Road
Akron, OH 44305
1-800-798-1554
Tel: (330) 798-9240
Fax: (330) 798-6968

Saint-Gobain Performance Plastics
5 rue du Dauphiné
Zone Industrielle de Chesnes
BP712 Saint-Quentin-Fallavier
Cedex, France 38297
Tel: (33) 0-4-74-94-82-34

Saint-Gobain Performance Plastics
1476 Kun Yang Road
Minghang Economic & Technological
Development Zone
Shanghai, China 200245
Tel: (86) 21-5472-1568
Fax: (86) 21-5472-2378/5472-2379

NOTE: The data and details given in this document are correct and up to date. This document is intended to provide information about the product and possible applications. This document is not the product specification and does not provide specific features, nor does it guarantee product performance in specific applications. Saint-Gobain cannot anticipate or control the conditions of the field and for this reason strongly recommends that practical tests are conducted to ensure that the product meets the requirements of a specific application.

Tygon S3™ is a trademark of Saint-Gobain Performance Plastics.